



Versatile!

- Diameters 4mm...16mm OD & 1/8...5/8 inch OD
- Highly flexible tubing
- Resistant to hydrolysis and microbes
- UV-resistant
- Food-safe
- FDA-listed material
- Kink-resistant
- Solid and translucent colors
- DUO tube available in Blue & Black

PUN-H - Solid Colors

ODD	Packed length	Packaging material	Blue	Black	Silver	Red	Green	Yellow
4 mm	50 m	Box	197383 ★	197390 ★	558278 ★	558285 ★	558292	558299
	500 m	Spool	558257 ★	558250 ★	558271 ★			
6 mm	50 m	Box	197384 ★	197391 ★	558279 ★	558286 ★	558293	558300
	500 m	Spool	558258 ★	558251 ★	558272 ★			
8 mm	50 m	Box	197385 ★	197392 ★	558280 ★	558287 ★	558294	558301
	400 m	Spool	558259 ★	558252 ★	558273 ★			
10 mm	50 m	Box	197386 ★	197393 ★	558281 ★	558288 ★	558295	558302
	300 m	Spool	558260 ★	558253 ★	558274 ★			
12 mm	50 m	Box	197387 ★	197394 ★	558282 ★	558289 ★	558296	558303
	200 m	Spool	558261 ★	558254 ★	558275 ★			
14 mm	50 m	Box	570386 ★	570387				
16 mm	50 m	Box	197388 ★	197395 ★	558283 ★	558290 ★	558297	558304
	100 m	Spool	558262 ★	558255	558276			
1/8 in	150 ft	Box	567945 ★	567953 ★	567937 ★		567977	
5/32 in	150 ft	Box	567946 ★	567954 ★				
	500 ft	Spool		568017				
1/4 in	150 ft	Box	567948 ★	567956 ★	567940 ★	567988	567980	567972
	500 ft	Spool	568014	568018	568010			
	1000 ft	Spool	568021	568023				
5/16 in	150 ft	Box	567949 ★	567957 ★				
	500 ft	Spool	568022	568024	568011			
3/8 in	150 ft	Box	567950 ★	567958 ★	567942 ★	567990	567982	567974
	500 ft	Spool	568016	568020				
1/2 in	150 ft	Box	567951 ★	567959 ★	567943 ★	567991	567983	567975
5/8 in	150 ft	Box	567952			567992	567984	567976

NOTE: Additional materials, sizes and colors are also available. Please contact Festo.



Polyurethane tubing - PUN-H

Packaging modes:



Spool



Box

PUN-H - Translucent Colors

OD	Packed length	Packing material	Natural (Clear)	Translucent blue	Translucent black	Translucent red	Translucent green	Translucent yellow
4 mm	50 m	Box	197376 ★	8048671 ★	8048673 ★	8048675	8048677	8048679
	500 m	Spool	558264 ★	8048672 ★	8048674 ★	8048676	8048678	8048680
6 mm	50 m	Box	197377 ★	8048681 ★	8048683 ★	8048685	8048687	8048689
	500 m	Spool	558265 ★	8048682 ★	8048684 ★	8048686	8048688	8048690
8 mm	50 m	Box	197378 ★	8048691 ★	8048693 ★	8048695	8048697	8048699
	400 m	Spool	558266 ★	8048692 ★	8048694 ★	8048696	8048698	8048700
10 mm	50 m	Box	197379 ★	8048701 ★	8048703 ★	8048705	8048707	8048709
	300 m	Spool	558267 ★	8048702 ★	8048704 ★	8048706	8048708	8048710
12 mm	50 m	Box	197380 ★	8048711 ★	8048713 ★	8048715	8048717	8048719
	200 m	Spool	558268 ★	8048712 ★	8048714 ★	8048716	8048718	8048720
14 mm	50 m	Box	570388					
16 mm	50 m	Box	197381 ★					
	100 m	Spool	558269					
1/8 in	150 ft	Box	567961 ★					
5/32 in	150 ft	Box	567962					
1/4 in	150 ft	Box	567964 ★	8203970	8203971	8203972	8203973	8203974
	500 ft	Spool	8003126					
5/16 in	150 ft	Box	567965 ★					
	500 ft	Spool	8003127					
3/8 in	150 ft	Box	567966 ★	8203975	8203976	8203977	8203978	8203979
	500 ft	Spool	8003128					
1/2 in	150 ft	Box	567967 ★	8203980	8203981	8203982	8203983	8203984

NOTE: Additional materials, sizes and colors are also available. Please contact Festo.

