


Valve series VG: VUVG / VTUG / VUWG

FESTO



The compact valve

Highlights

- Attractive price
- Compact design
- Festo quality
- High flow rate
- Short delivery times
- Pressure range up to 10 bar
- ...many more variants

Individual valves VUVG – for more power from a smaller design! Priceattractive, impressive and installed in a flash. Perfect for all high-speed applications requiring a particularly high flow combined with a compact size, e.g. in small parts assembly and electronics industry or in the food and packaging industry.

Short on space? Not a problem!

The VUVG is designed for small installation spaces.

Fast, safe, easy

When it comes to ordering, mounting and installation – thanks to captive screws, an integrated locking seal and a wide range of pre-assembled cables and electrical connections.

Small in size – big in power

The perfect footprint: for up to 100% more flow with higher energy density.

Click! Simply snap into place.

Modular electrical connection kit (E-box) with numerous connection options for optimum integration into your system concept.








VUVG-...-S with specific features

The new individual valve VUVG-...-S offers specific features in proven Festo quality at an attractive price. As part of the core product range, it is readily available worldwide from stock in large quantities and ready for dispatch in 24 hours!

Valve series VG: VUVG / VTUG / VUWG


Valve series in detail

The product series VUVG: chose and combine

Solenoid valve		VUVG-...-S	VUVG	Valve manifold VTUG			Pneumatic valve VUWG		
		 Focused features – Festo quality – attractive price							
Technical data									
Part of the core product range Our recommendation: look for the star									
Valve width [mm]		10	14	10	14	18	10	14	18
Valve function		2x 3/2, 5/2		5/2, 5/3, 2x 3/2					
Flow rate [l/min]		150, 360	660	100, 220, 380	780	1300	100, 220, 380	780	1300
Connections	Pneumatic	M5, M7	G1/8	M3 (QS 3/4) M5 (QS 3/4/6), M7 (QS 4/6)	G1/8 (QS 4/6/8)	G1/4 (QS 6/8/10)	M3 (QS 3/4) M5 (QS 3/4/6), M7 (QS 4/6)	G1/8 (QS 4/6/8)	G1/4 (QS 6/8/10)
	Electric	Non-modular 	Modular variant Plug connector, flying leads, cable, plug connector M8 (Cnomo: M12, type C) 			-			
Pressure range [bar]		1.5 ... 7		-0.9 ... 10					
Temperature range [°C]		-5 ... +50		-5 ... +60					
Voltage [V DC]		24		5, 12, 24			-		
Voltage [V AC]		-		-			Cnomo: 110, 230		
Protection class		IP40, IP65		IP40, IP65					

Standard: the non-detenting/detenting manual override for easy commissioning with cover if required.

 Integrated LED for 360° view – convenient for a fast status overview as well as reduced downtimes.




Imperial connections (inch sizes) can be easily realised with hybrid fittings.

Captive screws: strong and sturdy with high torque for secure mounting.

Locating lug for correct mounting of the valve.

Multiple pressure zones can be created quickly and easily with separators.

Captive seal integrated in the valve.

 **Festo core product range** covers 80% of your automation tasks

Worldwide: always in stock
Superb: Festo quality at an attractive price
Easy: just a few clicks to place an order online
Fast: generally ready for dispatch from the Festo factory in 24 hours

www.festo.com