


FESTO



Quickly available Round cylinder DSNU-S – Selected Products



- 1 Coupling piece KSG → page 3
- 2 Self-aligning rod coupler FK → page 3
- 3 Foot mounting HBN-S → page 3
- 4 One-way flow control valve GRLA → page 3
- 5 Push-in fitting NPQE → page 3
- 6 Mounting kit SMBR-8 → page 3
- 7 Proximity sensor SMT-8M/SDBT-MSX → page 4
Connecting cables NEBB → page 3



Festo core product range
Covers 80% of your automation tasks

Worldwide: Always in stock
Superb: Festo quality at an attractive price
Easy: Simplified procurement and warehousing
Fast: Usually ready for dispatch within 24 hours ex works

Check our electronic catalogue for components and solutions that go beyond our core tasks and functions.

→ www.festo.com/xdki

Or simply contact your Festo sales engineer. They'll be happy to help!

Order code – Basic design

001	002	003	004	005	006
DSNU	S				A

Legend: ☐ Mandatory entry

001	Type
DSNU	Round cylinder, double acting
002	Version
S	Space optimized

003	Piston Ø [mm]	004	Stroke [mm]
8	8	...	10, 15, 20, 25, 30, 40, 50, 60, 80, 100
12	12	...	10, 15, 20, 25, 30, 40, 50, 60, 80, 100, 125, 150
16	16	...	10, 15, 20, 25, 30, 40, 50, 60, 80, 100, 125, 150, 200
20	20	...	
25	25	...	

005	Cushioning
P	Elastic cushioning rings/plates at both ends
PPS	Pneumatic cushioning, self-adjusting at both ends
006	Position sensing
A	Via proximity sensor



Configurable product

This product and all its product options can be ordered online via the configurator:

→ www.festo.com/catalogue/...

Enter the part number or the type.

Part no.	Type	Part no.	Type
8112002	DSNU-S-8...	8112005	DSNU-S-20...
8112003	DSNU-S-12...	8112006	DSNU-S-25...
8112004	DSNU-S-16...		

Ordering – Basic design

004 Stroke [mm]	003 Piston Ø [mm]					003 Piston Ø [mm]		
	8	12	16	20	25	16	20	25
	005 Cushioning – 006 Position sensing					005 Cushioning – 006 Position sensing		
	P – A	P – A	P – A	P – A	P – A	PPS – A	PPS – A	PPS – A
10	★ 5205897	★ 5211896	★ 5216087	★ 5224633	★ 5228227			
15	★ 5205898	★ 5211897	★ 5216088	★ 5224634	★ 5228228			
20	★ 5205899	★ 5211898	★ 5216089	★ 5224635	★ 5228229			
25	★ 5205900	★ 5211899	★ 5216090	★ 5224636	★ 5228230	★ 5217238	★ 5225836	★ 5228452
30	★ 5205902	★ 5211900	★ 5216091	★ 5224637	★ 5228231	★ 5217239	★ 5225837	★ 5228453
40	★ 5205903	★ 5211901	★ 5216093	★ 5224639	★ 5228232	★ 5217240	★ 5225838	★ 5228454
50	★ 5205904	★ 5211903	★ 5216094	★ 5224641	★ 5228233	★ 5217241	★ 5225839	★ 5228455
60	★ 5205905	★ 5211904	★ 5216095	★ 5224642	★ 5228234	★ 5217242	★ 5225840	★ 5228456
80	★ 5205906	★ 5211905	★ 5216096	★ 5224643	★ 5228235	★ 5217243	★ 5225841	★ 5228457
100	★ 5205907	★ 5211906	★ 5216098	★ 5224644	★ 5228236	★ 5217244	★ 5225842	★ 5228458
125		★ 5211908	★ 5216099	★ 5224645	★ 5228237	★ 5217245	★ 5225843	★ 5228459
150		★ 5211909	★ 5216100	★ 5224646	★ 5228238	★ 5217246	★ 5225844	★ 5228460
200			★ 5216101	★ 5224647	★ 5228239	★ 5217248	★ 5225846	★ 5228461

Ordering – Accessories

1 Coupling piece KSG

For piston Ø [mm]	Part no.	Type
25	32963	KSG-M10x1,25



2 Self-aligning rod coupler FK

For piston Ø [mm]	Part no.	Type
8	6528	FK-M4
12, 16	★ 2061	FK-M6
20	★ 2062	FK-M8
25	★ 6140	FK-M10x1,25



3 Foot mounting HBN-S¹⁾

For piston Ø [mm]	Part no.	Type
8	★ 5407712	HBN-S-8x1
12, 16	★ 5407772	HBN-S-12/16x1
20, 25	★ 5407787	HBN-S-20/25x1
	★ 5407847	HBN-S-20/25x2



1) ...x1: . 1x foot; ...x2: 2x foot, 1x nut

4 One-way flow control valve GRLA

For piston Ø [mm]	Pneumatic connection	Tubing O.D. [mm]	Part no.	Type
Slotted head screw				
8, 12, 16	M5	3	★ 193137	GRLA-M5-QS-3-D
		4	★ 193138	GRLA-M5-QS-4-D
		6	★ 193139	GRLA-M5-QS-6-D
20, 25	G1/8	3	★ 193142	GRLA-1/8-QS-3-D
		4	★ 193143	GRLA-1/8-QS-4-D
		6	★ 193144	GRLA-1/8-QS-6-D
		8	★ 193145	GRLA-1/8-QS-8-D



5 Push-in fittings NPQE, straight shape

For piston Ø [mm]	Pneumatic connection	Tubing O.D. [mm]	Part no.	Type
Metric thread with sealing ring				
8, 12, 16	M5	3	8112908	NPQE-D-M5-Q3-P10
		4	8112909	NPQE-D-M5-Q4-P10
		6	8112910	NPQE-D-M5-Q6-P10
R thread				
20, 25	R1/8	4	8112913	NPQE-D-R18-Q4-P10
		6	8112914	NPQE-D-R18-Q6-P10
		8	8112915	NPQE-D-R18-Q8-P10
		10	8112916	NPQE-D-R18-Q10-P10
		12	8112917	NPQE-D-R18-Q12-P10



5 Push-in fittings NPQE, L-shape

For piston Ø	Pneumatic connection	Tubing O.D.	Part no.	Type
[mm]		[mm]		
Metric thread with sealing ring				
8, 12, 16	M5	3	8112937	NPQE-L-M5-Q3-P10
		4	8112938	NPQE-L-M5-Q4-P10
		6	8112939	NPQE-L-M5-Q6-P10
R thread				
20, 25	R1/8	4	8112942	NPQE-L-R18-Q4-P10
		6	8112943	NPQE-L-R18-Q6-P10
		8	8112944	NPQE-L-R18-Q8-P10
		10	8112945	NPQE-L-R18-Q10-P10
		12	8112946	NPQE-L-R18-Q12-P10



6 Mounting kit SMBR-8

For piston Ø [mm]	Part no.	Type
8	175091	SMBR-8-8
12	★ 175093	SMBR-8-12
16	★ 175094	SMBR-8-16
20	★ 175095	SMBR-8-20
25	★ 175096	SMBR-8-25



7 Connecting cable NEBB

Cable length [m]	Connection right	Part no.	Type
Connection left: straight socket, M8x1, 3-pin			
2.5	Cable, open end,	8066658	NEBB-M8G3-P-2.5-LE3
5	3-wire	8066659	NEBB-M8G3-P-5-LE3
Connection left: straight socket, M12x1, 5-pin			
2.5	Cable, open end,	8066670	NEBB-M12G5-P-2.5-LE3
5	3-wire	8066671	NEBB-M12G5-P-5-LE3
Connection left: angled socket, M8x1, 3-pin			
2.5	Cable, open end,	8066664	NEBB-M8W3-P-2.5-LE3
5	3-wire	8066665	NEBB-M8W3-P-5-LE3



Ordering – Accessories

7 Proximity sensors SMT-8M, for T-slot							
Measuring principle	Switching output	Electrical connection		Cable length [m]	Part no.	Type	
		Cable	Cable with plug, rotatable thread				
N/O contact							
Magneto-resistive	PNP	–	3-pin, M8x1	0.3	★ 574334	SMT-8M-A-PS-24V-E-0,3-M8D	
		3-wire	–	2.5	★ 574335	SMT-8M-A-PS-24V-E-2,5-OE	
		3-wire	–	5	★ 574336	SMT-8M-A-PS-24V-E-5,0-OE	
		–	3-pin, M12x1	0.3	★ 574337	SMT-8M-A-PS-24V-E-0,3-M12	
	NPN	3-wire	–	2.5	★ 574338	SMT-8M-A-NS-24V-E-2,5-OE	
		–	3-pin, M8x1	0.3	★ 574339	SMT-8M-A-NS-24V-E-0,3-M8D	
N/C contact							
Magneto-resistive	PNP	3-wire	–	7.5	★ 574340	SMT-8M-A-PO-24V-E-7,5-OE	

7 Proximity sensors SDBT-MSX, for T-slot, auto teach-in function							
Measuring principle	Switching output	Electrical connection		Cable length [m]	Part no.	Type	
		Cable	Cable with plug				
N/O default							
Magneto-resistive	PNP	–	3-pin, M8x1	0.3	8059123	SDBT-MSX-1L-PU-E-0.3-N-M8	
		3-wire	–	2.5	8059124	SDBT-MSX-1L-PU-E-2.5-N-LE	
		3-wire	–	5	8059125	SDBT-MSX-1L-PU-E-5-N-LE	
	NPN	–	3-pin, M8x1	0.3	8059120	SDBT-MSX-1L-NU-E-0.3-N-M8	
		3-wire	–	2.5	8059121	SDBT-MSX-1L-NU-E-2.5-N-LE	
		3-wire	–	5	8059122	SDBT-MSX-1L-NU-E-5-N-LE	

Additional accessories → www.festo.com/catalogue/dsnu

Worldwide always in stock:
the Festo core product range for automation



Festo core product range: Festo quality at an attractive price covering 80% of your automation tasks. From drives to accessories for factory automation as well as process automation – you can reduce procurement complexity for both the electric and pneumatic control chain.