




001	002	003	004	005	006
ADN					A
001	Type				
ADN	Standards-based cylinder, double-acting, based on ISO 21287				
002	Piston Ø [mm]				
---	12, 16, 20, 25, 32, 40, 50, 63, 80				
003	Stroke [mm]				
---	5, 10, 15, 20, 25, 30, 40, 50, 80				
004	Piston rod thread type				
A	Male thread				
I	Female thread				
005	Cushioning				
P	Elastic cushioning rings/plates at both ends				
006	Position sensing				
A	Via proximity switch				

Ordering – Basic design

003 Stroke [mm]	002 Piston Ø [mm]								
	12	16	20	25	32	40	50	63	80
	004 Piston rod with male thread – 005 Cushioning – 006 Position sensing								
	A-P-A								
5	536204 ★	536219 ★	536234 ★	536251 ★	536268 ★	536289 ★	536310 ★		
10	536205 ★	536220 ★	536235 ★	536252 ★	536269 ★	536290 ★	536311 ★	536332 ★	536353 ★
15	536206 ★	536221 ★	536236 ★	536253 ★	536270 ★	536291 ★	536312 ★	536333 ★	536354 ★
20	536207 ★	536222 ★	536237 ★	536254 ★	536271 ★	536292 ★	536313 ★	536334 ★	536355 ★
25	536208 ★	536223 ★	536238 ★	536255 ★	536272 ★	536293 ★	536314 ★	536335 ★	536356 ★
30	536209 ★	536224 ★	536239 ★	536256 ★	536273 ★	536294 ★	536315 ★	536336 ★	536357 ★
35	8178327 ★	8178762 ★	8178859 ★	574647 ★	576645 ★	8179031 ★	8178336 ★		
40	536210 ★	536225 ★	536240 ★	536257 ★	536274 ★	536295 ★	536316 ★	536337 ★	536358 ★
50	8178548	536331 ★	536241 ★	536258 ★	536275 ★	536296 ★	536317 ★	536338 ★	536359 ★
60			536352 ★	536373 ★	536276 ★	536297 ★	536318 ★	536339 ★	536360 ★
80					536277 ★	536298 ★	536319 ★	536340 ★	536361 ★
	004 Piston rod with female thread – 005 Cushioning – 006 Position sensing								
	I-P-A								
5	536211 ★	536226 ★	536242 ★	536259 ★	536278 ★	536299 ★	536320 ★		
10	536212 ★	536227 ★	536243 ★	536260 ★	536279 ★	536300 ★	536321 ★	536342 ★	536363 ★
15	536213 ★	536228 ★	536244 ★	536261 ★	536280 ★	536301 ★	536322 ★	536343 ★	536364 ★
20	536214 ★	536229 ★	536245 ★	536262 ★	536281 ★	536302 ★	536323 ★	536344 ★	536365 ★
25	536215 ★	536230 ★	536246 ★	536263 ★	536282 ★	536303 ★	536324 ★	536345 ★	536366 ★
30	536216 ★	536231 ★	536247 ★	536264 ★	536283 ★	536304 ★	536325 ★	536346 ★	536367 ★
35		8178765 ★	578011 ★	608920 ★	8179019 ★	8179033 ★	8178619 ★		
40	536217 ★	536232 ★	536248 ★	536265 ★	536284 ★	536305 ★	536326 ★	536347 ★	536368 ★
50	8178550 ★	536341 ★	536249 ★	536266 ★	536285 ★	536306 ★	536327 ★	536348 ★	536369 ★
60			536362 ★	536383 ★	536286 ★	536307 ★	536328 ★	536349 ★	536370 ★
80					536287 ★	536308 ★	536329 ★	536350 ★	536371 ★

