Pneumatic and electric modules of the valve terminal VTUG - the compact platform for your application

Fieldbus systems with CTEU

CANopen
CANopen was originally developed for the automotive industry by a joint venture led by Bosch.
It has been maintained by the organisation CiA (CAN in Automation) since 1995, and at the end of 2002 it was standardised as European standard EN 50325-4.

DeviceNet®
DeviceNet® is an open fieldbus standard that was developed by Rockwell Automation on the basis of the CAN protocol. DeviceNet® is standardised in European standard EN 50325.

CC-LINK®
"Control and Communications Link" (CC-Link) was developed by Mitsubishi Electric and has been available as an open fieldbus network since 1999.

PROFIBUS
Process Field Bus (PROFIBUS) is a fieldbus that was developed by Siemens and has been standardised in the IEC 61158 series of international standards. It enables communication between devices without the need for any specific adaptations to the interface.

EtherCAT®
EtherCAT® is a bus with real-time capability; it was developed by Beckhoff and the EtherCAT Technology Group (ETG).
EtherCAT® is an open technology and has been standardised in international standards IEC 61158 and IEC 61784 and in ISO 15745-4.

AS-Interface
AS-Interface is a manufacturer-independent, simple and sturdy installation system. It was developed and is represented by the AS-International Association, a loose association of a wide range of companies from different sectors.
AS-Interface has been standardised by IEC 62026-2 and EN 50295.

PROFINET
PROFINET by PROFIBUS and PROFINET International (PI) is the open industrial Ethernet standard for automation and is based on Ethernet TCP/IP and IT standards.
PROFINET technology is developed by Siemens and the PROFIBUS user organisation.
PROFINET is standardised in IEC 61158 and IEC 61784.

EtherNet/IP
EtherNet/IP was developed by Allen-Bradley (Rockwell Automation) and the ODVA (Open DeviceNet Vendor Association). EtherNet/IP is an open standard (technology based on Ethernet TCP/IT and UDP/IP) for industrial networks and is standardised in the IEC 61158 series of international standards.

VARAN
VARAN (Versatile Automation Random Network) is a real-time-capable Ethernet bus system that meets the highest requirements when it comes to flexibility and availability.
It is an open bus system developed by Austrian company Sigmatek.

IO-Link®
IO-Link® consists of a central master and the IO-Link® devices connected by special connecting cables. This permits a decentralised layout of the devices.

Festo installation system CPI
The CPI system is capable of meeting two completely different requirements and resolves the conflict between extensive decentralised modularisation and electrical installation. All CP valve terminals and CP modules are connected using a ready-to-install CP cable, and are attached to the CP interface. Every 4 modules make up an installation string that ends at the CP interface.

Reliable selection of fieldbus modules

Find the right module quickly
+ Reliable selection
+ Easy to order
→ **www.festo.com/catalogue/cteu**

Easy-to-search Support Portal

Online support
+ Product information
+ User documentation
+ Certificates
+ Software
→ **www.festo.com/sp/cteu**

Fieldbus nodes and Industrial Ethernet

Type	CTEU-CO	CTEU-DN	CTEU-CC	CTEU-PB	CTEU-PB-EX1C	CTEU-EC	CTEU-AS	CTEU-PN	CTEU-PN-EX1C	CTEU-EP	CTEU-VN	CTEU-CP
Part no.	570038	570039	1544398	570060	8107588	572556	572555	2201671	8107589	2798071	8087559	2169716
Protocol	CANopen	DeviceNet	CC-Link	PROFIBUS		EtherCAT		PROFINET		EtherNet/IP		Festo CP installation system
Connection technology	Sub-D					2x M12x1 socket, D-coded	1x socket (OUT), 1x plug (IN), M12x1, A-coded	2x M12x1 socket, D-coded		2x M12x1 socket, 4-pin, D-coded	2x M12x1 socket, D-coded	M9x0.5 socket, 5-pin
Degree of protection	IP65/IP67											
Inputs [bytes]	8	8	16	16		16	2	64		64	32	4
Outputs [bytes]	8	8	16	16		16	2	64		64	32	4
Other				I, OL us - Listed (OL)	For VTUG-VI-EX1E			I, OL us - Listed (OL)	For VTUG-VI-EX1E			

The system
- CTEU fieldbus modules for valve terminals
- Festo-specific interface (I-Port)
- Input modules CTSL for detecting sensor signals
- Interface for the Festo installation system CPI
- Direct and easy networking of valve terminals and other devices via a bus connection
- Wide range of applications with high IP65/67 degree of protection
- Universal connection technology (Sub-D, M12, terminal strip)
- Optional decentralised installation of the bus node for connecting two valve terminals
- Basic diagnostics: undervoltage, short circuit

CTEU for the universal use of valve terminals.

The fieldbus modules can be used for different valve terminal types with the Festo-specific, uniformly defined interface (I-Port).
The following protocols are currently supported:
+ CANopen
+ DeviceNet®
+ CC-LINK®
+ PROFIBUS
+ EtherCAT®
+ AS-Interface
+ PROFINET
+ EtherNet/IP
+ VARAN
+ Installation system CPI
+ IO-Link®

Electrical interfaces

Type	VAEM-L1-S-12-AP	VAEM-L1-S-24-AP	VAEM-L1-S-8-PT	VAEM-L1-S-16-PT	VAEM-L1-S-24-PT	VAEM-L1-S-8-PTL	VAEM-L1-S-16-PTL	VAEM-L1-S-24-PTL	VAEM-L1-S-M1-25	VAEM-L1-S-M1-25V2	VAEM-L1-S-M1-29V2	VAEM-L1-S-M1-29V4	VAEM-L1-S-M1-44	VAEM-L1-S-26-PTK	VAEM-L1-S-M3-26	VAEM-L1-S-M3-50
Part no.	8081922	8081923	573384	573939	573940	574207	574208	574209	573445	573447	573448	573449	573450	573446	On request: 573452	573451
Connection technology	Mini, D-coded		M12 part type B						Sub-D 25-pin						Flat cable 26-pin	Flat cable 50-pin
Protocol	IO-Link®								Parallel							
Electrical interface	CANopen, DeviceNet®, PROFIBUS, CC-LINK®, EtherCAT®, AS-Interface, PROFINET, EtherNet/IP, VARAN, Festo installation system CPI								Multi-pin plug							
Valve positions/ solenoid coils	12/24	24/48	8/16	16/32	24/48	8/16	16/32	24/48	Up to 24* - **Note:** a double solenoid valve occupies one valve position and two pins on the multi-pin plug. This means that the number of double solenoid valves per manifold rail is limited.							

Manifold rails

Manifold rails for semi-in-line valves, port 2 and 4 on the valve

Size	Port 2 and 4	Part no.	Order code
10	4 valve positions	573423	VABM-L1-10G-G18-4-GR
	5 valve positions	573424	VABM-L1-10G-G18-5-GR
	6 valve positions	573425	VABM-L1-10G-G18-6-GR
	7 valve positions	573426	VABM-L1-10G-G18-7-GR
	8 valve positions	573427	VABM-L1-10G-G18-8-GR
	9 valve positions	573428	VABM-L1-10G-G18-9-GR
	10 valve positions	573429	VABM-L1-10G-G18-10-GR
	12 valve positions	573430	VABM-L1-10G-G18-12-GR
	16 valve positions	573431	VABM-L1-10G-G18-16-GR
	20 valve positions	573432	VABM-L1-10G-G18-20-GR
	24 valve positions	573433	VABM-L1-10G-G18-24-GR
	8 double + 8 single solenoid valves	573927	VABM-L1-10G-G18-16-MGR
	6 double + 16 single solenoid valves	573928	VABM-L1-10G-G18-20-MGR
	24 single solenoid valves	573929	VABM-L1-10G-G18-24-MGR
14	4 valve positions	573500	VABM-L1-14G-G14-4-GR
	5 valve positions	573501	VABM-L1-14G-G14-5-GR
	6 valve positions	573502	VABM-L1-14G-G14-6-GR
	7 valve positions	573503	VABM-L1-14G-G14-7-GR
	8 valve positions	573504	VABM-L1-14G-G14-8-GR
	9 valve positions	573505	VABM-L1-14G-G14-9-GR
	10 valve positions	573506	VABM-L1-14G-G14-10-GR
	12 valve positions	573507	VABM-L1-14G-G14-12-GR
	16 valve positions	573508	VABM-L1-14G-G14-16-GR
	20 valve positions	573509	VABM-L1-14G-G14-20-GR
	24 valve positions	573510	VABM-L1-14G-G14-24-GR
	8 double + 8 single solenoid valves	573935	VABM-L1-14G-G14-16-MGR
	6 double + 16 single solenoid valves	573937	VABM-L1-14G-G14-20-MGR
	24 single solenoid valves	573938	VABM-L1-14G-G14-24-MGR

Manifold rails for sub-base valves, port 2 and 4 at the front

Size	Port 2 and 4	Part no.	Order code
10	4 valve positions	573434	VABM-L1-10HW-G18-4-GR
	5 valve positions	573435	VABM-L1-10HW-G18-5-GR
	6 valve positions	573436	VABM-L1-10HW-G18-6-GR
	7 valve positions	573437	VABM-L1-10HW-G18-7-GR
	8 valve positions	573438	VABM-L1-10HW-G18-8-GR
	9 valve positions	573439	VABM-L1-10HW-G18-9-GR
	10 valve positions	573440	VABM-L1-10HW-G18-10-GR
	12 valve positions	573441	VABM-L1-10HW-G18-12-GR
	16 valve positions	573442	VABM-L1-10HW-G18-16-GR
	20 valve positions	573443	VABM-L1-10HW-G18-20-GR
	24 valve positions	573444	VABM-L1-10HW-G18-24-GR
	8 double + 8 single solenoid valves	573930	VABM-L1-10HW-G18-16-MGR
	6 double + 16 single solenoid valves	573931	VABM-L1-10HW-G18-20-MGR
	24 single solenoid valves	573932	VABM-L1-10HW-G18-24-MGR
14	4 valve positions	573515	VABM-L1-14HW-G14-4-GR
	5 valve positions	573516	VABM-L1-14HW-G14-5-GR
	6 valve positions	573517	VABM-L1-14HW-G14-6-GR
	7 valve positions	573518	VABM-L1-14HW-G14-7-GR
	8 valve positions	573519	VABM-L1-14HW-G14-8-GR
	9 valve positions	573520	VABM-L1-14HW-G14-9-GR
	10 valve positions	573521	VABM-L1-14HW-G14-10-GR
	12 valve positions	573522	VABM-L1-14HW-G14-12-GR
	16 valve positions	573523	VABM-L1-14HW-G14-16-GR
	20 valve positions	573524	VABM-L1-14HW-G14-20-GR
	24 valve positions	573525	VABM-L1-14HW-G14-24-GR
	8 double + 8 single solenoid valves	573933	VABM-L1-14HW-G14-16-MGR
	6 double + 16 single solenoid valves	573934	VABM-L1-14HW-G14-20-MGR
	24 single solenoid valves	573935	VABM-L1-14HW-G14-24-MGR

Manifold rails for sub-base valves, for control cabinet installation, port 2 and 4 front

Size	Port 2 and 4	Part no.	Order code
10	Single supply	8058335	VABM-L1-10HW51-G18-4-GR
		8058336	VABM-L1-10HW51-G18-8-GR
	Double supply	8058338	VABM-L1-10HW51-G18-8-GR
		8058339	VABM-L1-10HW52-G18-12-GR
		8058340	VABM-L1-10HW52-G18-16-GR
		8058341	VABM-L1-10HW52-G18-24-GR
14	Single supply	8058342	VABM-L1-14HW51-G14-4-GR
		8058343	VABM-L1-14HW51-G14-8-GR
	Double supply	8058344	VABM-L1-14HW52-G14-8-GR
		8058345	VABM-L1-14HW52-G14-12-GR
		8058346	VABM-L1-14HW52-G14-16-GR
		8058347	VABM-L1-14HW52-G14-24-GR

Manifold rail

...for semi-in-line valves
The semi-in-line valves are supplied with external pilot air.
The pilot air is set via the manifold rail.
The scope of delivery of the manifold rail includes a short and a long blanking plug for setting the pilot air.

+ for semi-in-line valves MS/M7 (size 10), G1/8 (size 14) and G1/4 (size 18)
+ for 2x 3/2-way, 5/2-way and 5/3-way valves
+ 4 to 24 valve positions including special fire electrical links.

...for sub-base valves
The sub-base valves are supplied with external pilot air.
The pilot air is set via the manifold rail.
The scope of delivery of the manifold rail includes a short and a long blanking plug for setting the pilot air.

+ for sub-base valves MS/M7 (size 10), G1/8 (size 14) and G1/4 (size 18)
+ for 3/2-way, 2x 3/2-way, 5/2-way and 5/3-way valves
+ 4 to 24 valve positions with electrical links

...for long version
I-port interface variant on the side:
For semi-in-line valves and sub-base valves, MS/M7 (size 10), G1/8 (size 14) and G1/4 (size 18)

Interlock variant:
The interlock function enables the first 16 solenoid coils to be individually supplied externally.
The external supply guarantees the safety-related enabling of these valves.
For sub-base and semi-in-line valves MS1/M7 (size 10)

More information on the long version:
→ **www.festo.com/catalogue/vtug**

Connecting cables for multi-pin connection

Type	NEBV-S1G25-K-2.5-N-LE25-S6	NEBV-S1G25-K-5-N-LE25-S6	NEBV-S1G25-K-10-N-LE25-S6	NEBV-S1G44-K-2.5-N-LE44-S6	NEBV-S1G44-K-5-N-LE44-S6	NEBV-S1G44-K-10-N-LE44-S6	NEBV-S1WA25-K-2.5-N-LE25-S9	NEBV-S1WA25-K-5-N-LE25-S9	NEBV-S1WA25-K-10-N-LE25-S9	NEBV-S1WA44-K-2.5-N-LE44-S9	NEBV-S1WA44-K-5-N-LE44-S9	NEBV-S1WA44-K-10-N-LE44-S9
Part no.	575417	575418	575419	575112	575113	575115	575105	575106	575107	575108	575109	575110
Electrical connection	Sub-D socket, straight						Sub-D socket, angled					
Other	25-pin, up to 2x cells, open cable end, 25-core			44-pin, up to 4x cells, open cable end, 44-core			25-pin, up to 2x cells, open cable end, 25-core			44-pin, up to 4x cells, open cable end, 44-core		
Degree of protection	IP40						IP65					

Valve terminal configurator
A valve terminal configurator is available online to help you select a suitable valve terminal.
Select a valve terminal with I-Port interface and order the relevant CTEU bus nodes. The bus nodes then only need to be placed on the valve terminal.
The ident. code for the valve terminals specifies the valve functions, the number of valves, the vacant valve positions as well as the additional functions and the type of compressed air supply.

As is the case with all Festo products, all valve terminals are supplied:
+ Fully pre-assembled
+ Equipped with fittings on request
+ Tested for electrical functionality
+ Tested for pneumatic functionality
+ Securely packaged
+ User documentation can be downloaded free of charge

→ **www.festo.com/catalogue/vtug**

Plug connector for fieldbus connection

Type	FBS-SUB-9-BU-2x5POL-B	FBS-SUB-9-GS-2x6POL-B	FBS-SUB-9-GS-DP-B	NECU-M-S-D12G4-C2-ET	NEFU-X2AF-M12GA	NEFU-X22F-M12GA
Part no.	532719	532720	532216	563109	577226	577225
Electrical connection	9-pin socket, Sub-D, straight	9-pin plug, Sub-D, straight		M12x1 plug, 4-pin, D-coded	4-pin socket, M12x1, A-coded	
Cable fitting	PG9					
Degree of protection	IP65/67 (mounted)					
Other					Cable socket with load voltage supply	Cable socket without load voltage supply
Protocol	CANopen, DeviceNet, CC-Link, PROFIBUS, EtherCAT, EtherNet/IP					

Connection technology for IO-Link®

Type	FB-TA-M12-5POL	SEA-M12-5GS-PG7	NEDU-L1R2-M12G5-M12LE-1R
Part no.	171175	175487	8095516
Electrical connection	M12 T-adapter, 5-pin	Straight plug, M12, 5-pin	Y-distributor with cable on controller side, M12x1 A-coded
Other	For IO-Link®and load supply	For T-adapter FB-TA	For IO-Link master with port type A

More state-of-the-art electrical connection technology:
You will find our extensive range of connecting cables, distributors and plugs online:

Connecting cables **NEBV** → **www.festo.com/catalogue/nebv**
Distribution cables **FBD** → **www.festo.com/catalogue/fbs**
Sensor plug **NEFU** → **www.festo.com/catalogue/nefu**

HIGHLIGHT: Universal connecting cables NEBU
→ **www.festo.com/catalogue/nebu**

ELECTRICAL CONNECTION TECHNOLOGY


Valve terminal VTUG with multi-pin plug connection


Valve terminal VTUG with I-Port as the basis for bus nodes (CTEU)


Valve terminal VTUG with I-Port and mounted bus node


Valve terminal VTUG with I-Port for control cabinet installation, Outlet direction front (FO)

The range of capabilities

Innovative
+ Festo-specific I-Port interface for bus nodes (CTEU)
+ IO-Link® mode for direct connection to a higher-level IO-Link master
+ Festo-specific I-Port interface with interlock
+ Variable multi-pin connection by Sub-D or ribbon cable
+ Reversible piston spool valves, up to 24 valve positions
+ Reduced power consumption
+ Excellent price/performance ratio.

Flexible
+ Choice of quick push-in connectors
+ Multiple pressure zones possible
+ Sub-D variant and fieldbus interface degree of protection IP67
+ Internal or external pilot air with the same manifold rail possible by using blanking plugs
+ Sub-base valves with working ports facing downwards for control cabinet installation

Operational safety
+ Sturdy and durable metal components
  •Valves
  •Manifold rails
+ Quick troubleshooting with LED display
+ Manual override:
  •Non-detenting
  •detenting
  •Covered

Easy to assemble
+ Easy assembly with captive screws and seal
+ Easy-to-change connection technology
+ Inscription label holders for labelling

ELECTRICS

PNEUMATICS


Fig.: Sample valve terminal VTUG

ALTERNATIVE: Compact sintered silencers AMTE
→ **www.festo.com/catalogue/amte**

Reliable configuration

The quick way to your VTUG
+ Reliable to configure
+ Easy to order
→ **www.festo.com/catalogue/vtug**

Easy-to-search Support Portal

Online support
+ Product information
+ User documentation
+ Certificates
+ Software
→ **www.festo.com/sp/vtug**

Valves

Size	Ports 2 and 4	Order code Start	Configurator order code	3/2-way valve, normally closed	3/2-way valve, normally open	3/2-way valve, normally closed	3/2-way valve, normally open	2x 3/2-way valve, normally closed	2x 3/2-way valve, normally open	2x 3/2-way valve, normally open, normally open position - 1x closed - 1x open	2x 3/2-way valve, normally open	2x 3/2-way valve, normal position - 1x closed - 1x open	5/2-way valve, single solenoid	5/2-way valve, single solenoid	5/2-way valve, single solenoid	5/2-way valve, double solenoid	5/3-way valve, mid-position closed	5/3-way valve, mid-position pressurised	5/3-way valve, mid-position exhausted
Semi-in-line valves																			
10	M5	Part no.		–	–	–	–	573386	573387	573388	573389	573390	573391	–	573393	573392	573394	573395	573397	573396
		Order code	VUVG-S10-...	–	–	–	–	T32C-AZT-M5-1T1L	T32U-AZT-M5-1T1L	T32H-AZT-M5-1T1L	T32C-MZT-M5-1T1L	T32H-MZT-M5-1T1L	T32H-AZT-M5-1T1L	–	M32-AZT-M5-1T1L	B32-ZT-M5-1T1L	B32-ZT-M5-1T1L	P3SC-ZT-M5-1T1L	P3SU-ZT-M5-1T1L	P3SH-ZT-M5-1T1L
		Pilot air supply		–	–	–	–	External	External	External	External	External	External	–	External	External	External	External	External	External
		Reset method		–	–	–	–	Pneumatic spring	Pneumatic spring	Pneumatic spring	Mechanical spring	Mechanical spring	Mechanical spring	–	Pneumatic/mechanical spring	Pneumatic/mechanical spring	–	Mechanical spring	Mechanical spring	Mechanical spring
	M7	Part no.		–	–	–	–	573398	573399	573400	573401	573402	573403	–	573405	573404	573406	573407	573409	573408
		Order code	VUVG-S10-...	–	–	–	–	T32C-AZT-M7-1T1L	T32U-AZT-M7-1T1L	T32H-AZT-M7-1T1L	T32C-MZT-M7-1T1L	T32U-MZT-M7-1T1L	T32H-MZT-M7-1T1L	–	M72-MZT-M7-1T1L	B72-MZT-M7-1T1L	B52-ZT-M7-1T1L	P3SC-ZT-M7-1T1L	P3SU-ZT-M7-1T1L	P3SH-ZT-M5-1T1L
		Pilot air supply		–	–	–	–	External	External	External	External	External	External	–	External	External	External	External	External	External
		Reset method		–	–	–	–	Pneumatic spring	Pneumatic spring	Pneumatic spring	Mechanical spring	Mechanical spring	Mechanical spring	–	Pneumatic/mechanical spring	Pneumatic/mechanical spring	–	Mechanical spring	Mechanical spring	Mechanical spring
14	G1/8	Part no.		–	–	–	–	573366	573367	573368	573369	573370	573419	–	573371	–	573423	573373	573375	573374
		Order code	VUVG-S14-...	–	–	–	–	T32C-AZT-G18-1T1L	T32U-AZT-G18-1T1L	T32H-AZT-G18-1T1L	T32C-MZT-G18-1T1L	T32U-MZT-G18-1T1L	T32H-MZT-G18-1T1L	–	M32-AZT-G18-1T1L	B32-ZT-G18-1T1L	B32-ZT-G18-1T1L	P3SC-ZT-G18-1T1L	P3SU-ZT-G18-1T1L	P3SH-ZT-G18-1T1L
		Pilot air supply		–	–	–	–	External	External	External	External	External	External	–	External	External	External	External	External	External
		Reset method		–	–	–	–	Pneumatic spring	Pneumatic spring	Pneumatic spring	Mechanical spring	Mechanical spring	Mechanical spring	–	Pneumatic spring	Pneumatic spring	–	Mechanical spring	Mechanical spring	Mechanical spring
18	G1/4	Part no.		–	–	–	–	8004873	8004874	8004875	8004876	8004877	8004878	–	8004879	8004880	–	8004881	8004882	8004883	8004884
		Order code	VUVG-S18-...	–	–	–	–	T32C-AZT-G14-1T1L	T32U-AZT-G14-1T1L	T32H-AZT-G14-1T1L	T32C-MZT-G14-1T1L	T32U-MZT-G14-1T1L	T32H-MZT-G14-1T1L	–	M32-AZT-G14-1T1L	M32-MZT-G14-1T1L	–	B32-ZT-G14-1T1L	P3SC-ZT-G14-1T1L	P3SU-ZT-G14-1T1L	P3SH-ZT-G14-1T1L
		Pilot air supply		–	–	–	–	External	External	External	External	External	External	–	External	External	–	External	External	External	External
		Reset method		–	–	–	–	Pneumatic spring	Pneumatic spring	Pneumatic spring	Mechanical spring	Mechanical spring	Mechanical spring	–	Pneumatic spring	Mechanical spring	–	Mechanical spring	Mechanical spring	Mechanical spring	Mechanical spring
Sub-base valves																			
10	M5/M7	Part no.		8028231	8028232	–	–	573410	573411	573412	573413	573414	573415	–	573417	573416	573418	573419	573421	573420
		Order code	VVVG-B10-...	Z-M32C-AZT-F-1T1L	Z-M32U-AZT-F-1T1L	–	–	T32C-AZT-F-1T1L	T32U-AZT-F-1T1L	T32H-AZT-F-1T1L	T32C-MZT-F-1T1L	T32U-MZT-F-1T1L	T32H-MZT-F-1T1L	–	M32-MZT-F-1T1L	M32-AZT-F-1T1L	B32-ZT-F-1T1L	P3SC-ZT-F-1T1L	P3SU-ZT-F-1T1L	P3SH-ZT-F-1T1L
		Pilot air supply		External	External	–	–	External	External	External	External	External	External	–	External	External	External	External	External	External	External
		Reset method		Pneumatic/mechanical spring	Pneumatic/mechanical spring	–	–	Pneumatic spring	Pneumatic spring	Pneumatic spring	Mechanical spring	Mechanical spring	Mechanical spring	–	Pneumatic/mechanical spring	Pneumatic/mechanical spring	–	Mechanical spring	Mechanical spring	Mechanical spring	Mechanical spring
14	G1/8	Part no.		8028235	8028236	–	–	573476	573477	573478	573479	573480	573481	573482	573483	–	573484	573485	573487	573486
		Order code	VUVG-B14-...	Z-M32C-AZT-F-1T1L	Z-M32U-AZT-F-1T1L	–	–	T32C-AZT-F-1T1L	T32U-AZT-F-1T1L	T32H-AZT-F-1T1L	T32C-MZT-F-1T1L	T32U-MZT-F-1T1L	T32H-MZT-F-1T1L	M32-AZT-F-1T1L	M32-MZT-F-1T1L	–	B32-ZT-F-1T1L	P3SC-ZT-F-1T1L	P3SU-ZT-F-1T1L	P3SH-ZT-F-1T1L
		Pilot air supply		External	External	–	–	External	External	External	External	External	External	External	External	External	–	External	External	External	External
		Reset method		Pneumatic/mechanical spring	Pneumatic/mechanical spring	–	–	Pneumatic spring	Pneumatic spring	Pneumatic spring	Mechanical spring	Mechanical spring	Mechanical spring	Pneumatic/mechanical spring	Pneumatic/mechanical spring	Pneumatic/mechanical spring	–	Mechanical spring	Mechanical spring	Mechanical spring	Mechanical spring
Sub-base valves copper-, zinc-, nickel-free – recommended for production plants for manufacturing Li-ion batteries (F1A)																			
10	M5/M7	Part no.		–	–	–	–	8150599	8141516	8141517	8141518	8141519	8141520	–	8150460	8150397	8150398	8141521	8141523	8141522
		Order code	VVVG-B10-...	–	–	–	–	T32C-AZT-F-1T1L-F1A	T32U-AZT-F-1T1L-F1A	T32H-AZT-F-1T1L-F1A	T32C-MZT-F-1T1L-F1A	T32U-MZT-F-1T1L-F1A	T32H-MZT-F-1T1L-F1A	–	M32-AZT-F-1T1L-F1A	B32-ZT-F-1T1L-F1A	B32-ZT-F-1T1L-F1A	P3SC-ZT-F-1T1L-F1A	P3SU-ZT-F-1T1L-F1A	P3SH-ZT-F-1T1L-F1A
		Pilot air supply		–	–	–	–	External	External	External	External	External	External	–	External	External	External	External	External	External	External
		Reset method		–	–	–	–	Pneumatic spring	Pneumatic spring	Pneumatic spring	Mechanical spring	Mechanical spring	Mechanical spring	–	Pneumatic/mechanical spring	Pneumatic/mechanical spring	–	Mechanical spring	Mechanical spring	Mechanical spring	Mechanical spring
14	G1/8	Part no.		–	–	–	–	8150602	8141527	8141528	8141529	8141530	8141531	8150400	8150467	–	8150403	8141532	8141536	8141533
		Order code	VVVG-B14-...	–	–	–	–	T32C-AZT-F-1T1L-F1A	T32U-AZT-F-1T1L-F1A	T32H-AZT-F-1T1L-F1A	T32C-MZT-F-1T1L-F1A	T32U-MZT-F-1T1L-F1A	T32H-MZT-F-1T1L-F1A	M32-AZT-F-1T1L-F1A	M32-MZT-F-1T1L-F1A	–	B32-ZT-F-1T1L-F1A	P3SC-ZT-F-1T1L-F1A	P3SU-ZT-F-1T1L-F1A	P3SH-ZT-F-1T1L-F1A
		Pilot air supply		–	–	–	–	External	External	External	External	External	External	External	External	–	External	External	External	External	External	External
		Reset method		–	–	–	–	Pneumatic spring	Pneumatic spring	Pneumatic spring	Mechanical spring	Mechanical spring	Mechanical spring	Pneumatic spring	Pneumatic spring	–	Mechanical spring	Mechanical spring	Mechanical spring	Mechanical spring	Mechanical spring

**** Suitability for the production of Li-ion batteries:**
Metals with more than 1% by mass of copper, zinc or nickel are excluded from use. Exceptions are nickel in steel, chemically nickel-plated surfaces, circuit boards, cables, electrical plug connectors and coils.

Key features

Basic valves VUVG
Sizes 10, 14 and 18
Designed as semi-in-line or sub-base valves
Reversible piston spool valves
Up to 24 valve positions

Valve functions

3/2-way valve
+ Single solenoid
+ Normally open
+ Normally closed
+ Pneumatic
+ Pneumatic/mechanical spring

2x 3/2-way valve
+ Single solenoid
+ Normally open
+ Normally closed
+ 1x normally closed, 1x normally open
+ Mechanical spring
+ Pneumatic spring

5/2-way valve
+ Single, double solenoid valve
+ Pneumatic/mechanical spring
+ Mechanical spring
+ Pneumatic spring

5/3-way valve
+ Mid-position pressurised
+ Mid-position exhausted
+ Mid-position closed

Types of valves

Semi-in-line valve
The supply ports (1, 3 and 5) for semi-in-line valves are connected to the valve by common pneumatic links (e.g. sub-base).
The working ports (2, 4) are on the valve.

Sub-base valve
In the case of sub-base valves, the supply ports (1, 3 and 5) and the working ports (2, 4) are connected to the valve via pneumatic links (e.g. sub-base).
The working ports (2, 4) are located on the sub-base.

...for mounting

Type	NHH-35-2000	VAME-T-M4	VAME-T-M4-F1A	VAME-L1-Q
Designation	H-rail	H-rail mounting		Mounting bracket
Part no.	35430	569998	8162649	8156059
Function/note	Length 2 m		For production plants for manufacturing lithium-ion batteries	Mounting bracket, right and left, with screw set for sub-base valve (control cabinet installation). Mounting is possible only with VTUG-in size 10 and size 14.
		Use the following screws for mounting: Size 10: DIN 912: M4x30 Size 14: DIN 912: M4x40 Size 18: DIN 912: M5x50		

...for manual override (MO)

Type	VMPA-HBV-B	VMPA-HBT-B	VAMC-L1-CO	ASLR-D-L12
Designation	Cover cpis for MO			Identification support
Part no.	540899	540897	8002234	570818
Function	Covered	Non-detenting	Detenting (without accessories)	Fitted onto the MO

Separators – for creating several pressure zones in the manifold rail

Type	VABD-G-B	VABD-6-B-F1A	VABD-B-B	VABD-B-B-F1A	VABD-10-B	VABD-10-B-F1A	VABD-12-B	VABD-12-B-F1A
Application with...	Sub-base valves		Semi-in-line valves		All manifold rails			
Part no.	569996	8154678	569995	8154679	569996	8154680	569997	8154681
Size	10, MS/M7				14		18	
Note		Copper-, zinc-, nickel-free		Copper-, zinc-, nickel-free		Copper-, zinc-, nickel-free		Copper-, zinc-, nickel-free

Supply plates – additional air supply/exhaust via a valve position (connections for ports 1, 3 and 5).

Type	VABF-L1-10-P3A4-M7-T1	VABF-L1-10-P3A4-M7-T1-F1A	VABF-L1-14-P3A4-G18-T1	VABF-L1-14-P3A4-G18-T1-F1A	VABF-L1-18-P3A4-G16-T1
Order code config.	S				
Additionally for...	Port 1, 3 and 5				
Part no.	573924	8141539	573925	8141540	8004898
Size	10		14		18
Note	Copper-, zinc-, nickel-free		Copper-, zinc-, nickel-free		

Hoods

Type	CAFC-X1-GAL-200-Z	CAFC-X1-GAL-300-Z	CAFC-X1-GAL-400-Z	CAFC-X1-GAL-600-Z	CAFC-X1-GAL-600-Z	CAFM-X1-B-200	CAFM-X1-B-300	CAFM-X1-B-400	CAFM-X1-B-500	CAFM-X1-B-600	CAFC-X1-BE
Designation	Hood section including mounting attachments for connecting several hood sections in series					Profile strip for mounting the hood					Mounting kit
Part no.	8127858	8127859	8127860	8127862	8127862	3307385	3307386	3307387	3307388	3307389	572257
Application with...	VTUG-10-4 sections	VTUG-10-8/12-14-4 sections	VTUG-10-16/24-14-8/12 sections	VTUG-14-16 sections	VTUG-14-24 sections						
Length [mm]	200	300	400	600		196	296	396	496	596	

The VTUG-VI-EX1 hood CAFC is a space- and cost-saving alternative to a control cabinet.
+ Impact protection (min. 7 J) for the modules underneath in combination with a suitable mounting plate provided by the user
+ Protection against electrostatic discharge by using electrically conductive materials and the option of connecting an earth wire
+ Protection against disconnection of live plugs (by securing the hood with at least one special fastener in accordance with EN 60079-0, 9.2 and 20)
+ UV protection for the VTUG modules underneath

Cover plates for empty valve positions (reserve position)

Type	VABB-L1-10-T	VABB-L1-10-T-F1A	VABB-L1-14-T	VABB-L1-14-T-F1A	VABB-L1-18-T
Order code config.					
Designation	Vacant position				
Part no.	573422	8141537	573488	8141538	8004897
Size	10		14		16
Note	Copper-, zinc-, nickel-free		Copper-, zinc-, nickel-free		

Silencer

Type	AMTE-M-LH-M3	AMTE-M-LH-M5	U-1/8	U-1/4	U-1/4-20 (20 pieces)	UC-M7	UC-1/8	UC-1/4	UC-1/4-20 (20 pc.)
Version	Sintered metal		Plastic						
Part no.	1233120	120858	2307	2316	534223